


PHOTOMETRY


LR5/1.9 - LR6 Symmetric

48" Long Test Sample
Clear acrylic lens*




LR5/1.9 - LR6 Asymmetric

48" Long Test Sample
Clear acrylic lens*



LR5/1.9 - LR6 Asymmetric/30°

48" Long Test Sample
Clear acrylic lens*



*.72 Frosted lens multiplier

Photometry downloads (zip compressed files)

LR5

[LR5-1.9 Symmetric, Clear lens](#) - Standard

[LR5-1.9 Symmetric, Frosted lens](#) (-FL)

[LR5-1.9 Asymmetric, 30° tilt](#) (-ASYM/30°)

[LR5-1.66/1.5 Symmetric](#) - Standard

[LR5-1.66/1.5 Symmetric](#) (-LED/HO)

LR6

[LR6-1.5 Symmetric, Clear lens](#) - Standard

[LR6-1.5 Symmetric, Frosted lens](#) (-FL)

[LR6-1.5 Asymmetric, 30° tilt](#) (-ASYM/30°)

